

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200940044](#)
Status: **Active**
Overview: Brad M23 Signal and Power Connectors
Description: Brad M23 Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 18/22 AWG, PUR Cable, 10.0m (32.81') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120094
Connector End A	M23
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Protocol	N/A
Region	America, Asia, Europe
Taxonomy	Circular Industrial Cordsets
Type	Single Ended
UPC	78172553801

Physical

Cable Diameter	11.43mm (.450")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	19
Temperature Range - Operating	-25° to +90°C
Wire Size AWG	18, 22
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	63V AC/DC

Material Info

Engineering Number	K03001P80M100
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	1200940044-000, SD-120094-002-001
---------------	-----------------------------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000408918_00_000.pdf

CER_4000410292_00_000.pdf

Search Parts in this Series

[120094 Series](#)