

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201150002](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: MPIS Micro-Change (M12) Passive Junction Box, Side Mount, 4 Ports, LED for PNP Sensor, with Mini-Change 12 Pole Home Run Connector

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Passive Distribution Boxes
 Series [120115](#)
 IP Rating IP67
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (M12)
 Taxonomy Passive Distribution Boxes
 UPC 78678840842

Physical

Bus I/O Micro-Change (M12)
 Cable Connector Orientation N/A
 Home Run Cable Length N/A
 Home Run Connector Mini-Change - 12 pole
 Home Run Interface Integrated Connector
 Keyway A-coded
 LED Indicator PNP Sensors
 Material - Cable Jacket N/A
 Orientation Side Mount
 Poles 5
 Poles (wired) 4
 Ports 4
 Temperature Range - Operating -25°C to +90°C
 Wiring Configuration Single I/O per Port

Electrical

Current - Maximum per Contact 4.0A
 Functional Wiring PNP
 Voltage - Maximum 10-30V DC

Material Info

Engineering Number BSY401P-FBB

Reference - Drawing Numbers

Sales Drawing 1201150002-000



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[120115 Series](#)