

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1210360056](#)

**Status:** **Active**

**Overview:** [mPm DIN Valve Connectors](#)

**Description:** Micro-Change (M12) to Brad mPm DIN Form B - 10mm, 2 Pole Plus Ground with C4 Circuit, 24V, Yellow LED, Shielded PUR Black, 5 Poles, Male (Straight), 0.60m (1.97') Length, 24V

**Documents:**

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	<a href="#">121036</a>
Connector End A	Brad mPm DIN B - 10mm
Connector End B	Micro-Change (M12)
IP Rating	IP65
Material - Contact	Brass
Overview	<a href="#">mPm DIN Valve Connectors</a>
Product Name	Micro-Change (M12), mPm
Protocol	N/A
Region	America, Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	78678850263

**Physical**

Cable Diameter	5.72mm (.225")
Cable Length	0.60m (1.97')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Male
Keyway	Single
LED Indicator	Yellow
Material - Cable Jacket	PUR
Material - Connector Body	Polypropylene
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	22.000/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +75°C
Wire Size AWG	20
Wire/Cable Type	PUR

**Electrical**


Current - Maximum per Contact	1.5A
Voltage - Maximum	24V

**Material Info**

Engineering Number	D850B0P12M006
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-121036-005-001
---------------	-------------------



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[121036 Series](#)