

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210502011](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form C - 8mm, 2 Pole Plus Ground, to 5.0m (16.40') PUR UL Cable Pigtail, Yellow LED, Black Nitrile Gasket, 24V

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E218123

General

Product Family Industrial Cordsets
 Series [121050](#)
 Connector End A Brad mPm DIN C - 8mm
 Connector End B Pigtail
 IP Rating IP65
 Material - Contact Brass
 Overview [mPm DIN Valve Connectors](#)
 Product Name mPm
 Protocol N/A
 Region America, Europe
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 883906587673

Physical

Cable Diameter 5.72mm (.225")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Male-Pigtail
 Keyway None
 LED Indicator Yellow
 Material - Cable Jacket PUR UL
 Material - Connector Body Polypropylene
 Material - Coupling Nut N/A
 Material - Plating Mating Gold
 Orientation 90° to Pigtail
 Poles 2
 Temperature Range - Operating -40° to +90°C
 Wire Size AWG 20
 Wire/Cable Type N/A

Electrical

Current - Maximum per Contact N/A
 Voltage - Maximum 24V

Material Info

Engineering Number E492B2A50011C4H

Reference - Drawing Numbers

Sales Drawing SD-121050-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[121050 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION