

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210503398](#)

Status: **Active**

Overview: mPm DIN Valve Connectors

Description: mPm DIN Valve Connector, Form C - 8mm, 2 Pole Plus Ground, to 5.0m (16.40') PUR UL Cable Pigtail, Yellow LED, Black Nitrile Gasket, 115V

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	121050
Connector End A	Brad mPm DIN C - 8mm
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Protocol	N/A
Region	America, Europe
Taxonomy	Circular Industrial Cordsets
Type	Single Ended
UPC	78172534610

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	PUR UL
Material - Connector Body	Polypropylene
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire Size AWG	20
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	115V

Material Info

Engineering Number E492B2A50011S0L

Reference - Drawing Numbers

Sales Drawing SD-121050-002-001



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[121050 Series](#)