

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1211290237](#)  
**Status:** **Active**  
**Overview:** mPm DIN Valve Connectors  
**Description:** mPm DIN Screw M3 Steel-Zinc Plated with Additional Sealing Grommet, 27.00mm Length, 1 Bag of 100

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-121129-001-001 \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">121129</a>
IP Rating	IP65, IP67
Material - Contact	N/A
Overview	<a href="#">mPm DIN Valve Connectors</a>
Product Name	mPm
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	884982071575

**Physical**

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Orientation	N/A
Pitch - Mating Interface	N/A
Poles	N/A
Temperature Range - Operating	N/A
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

**Material Info**

Engineering Number	3000-90
--------------------	---------

**Reference - Drawing Numbers**

Packaging Specification	PK-121129-001-001
Sales Drawing	SD-121129-237-001

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[121129 Series](#)