

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300000046](#)
Status: **Active**
Overview: [Brad Quick-Change Connectors](#)
Description: Quick-Change Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 1.83m (6.0') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E46237

General

Product Family Industrial Cordsets
 Series [130000](#)
 Connector End A Quick-Change
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad Quick-Change Connectors](#)
 Product Name Quick-Change
 Region America
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 78678832350

Physical

Cable Diameter 16.63mm (.655")
 Cable Length 1.83m (6.0')
 Color - Cable Jacket Yellow
 Coupling Style Threaded
 Gender Female-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket CPE
 Material - Connector Body TPE
 Material - Coupling Nut Nylon
 Material - Plating Mating N/A
 Net Weight 425.000/g
 Orientation Straight to Pigtail
 Poles 3
 Temperature Range - Operating -20° to +105°C
 Wire Size AWG 12
 Wire/Cable Type SOW

Electrical

Current - Maximum per Contact 25.0A
 Voltage - Maximum 600V

Material Info

Engineering Number 32350

Reference - Drawing Numbers

Sales Drawing 1300000045-000



Series image - Reference only

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

Not Relevant

Compliant with Exemption 3

RoHS Phthalates

ZZCERT_UKCA

Not Contained

CER_4000410546_00_000.pdf

- Declaration of Conformity

Search Parts in this Series

[130000 Series](#)

This document was generated on 10/14/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION