

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300130541](#)
Status: **Active**
Overview: [minichange_products](#)
Description: Mini-Change Receptacle, 5 Pole, Male to Female Pass Thru

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Field Attachable / Accessories
 Series [130013](#)
 IP Rating IP67
 Overview [minichange_products](#)
 Product Name Mini-Change®
 Type Field Attachable Connector

Physical

Cable Diameter N/A
 Coupling Type External Thread
 Diagnostics / LEDs No
 Diagnostics Port No
 Gender Male-Female
 Keyway Single
 Material - Connector Body Nickel-plated Brass
 Material - Contact Brass
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold over Nickel
 Orientation Straight
 Poles 5
 Temperature Range - Operating -20°C to +60°C
 Wire Size AWG N/A

Electrical

Current - Maximum per Contact 8A
 Voltage - Maximum 600V AC/DC

Material Info

Old Part Number 1R5030

Reference - Drawing Numbers

Sales Drawing SD-130013-012

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[130013Series](#)