

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300130589](#)

**Status:** **Active**

**Overview:**

**Description:** Mini-Change A-Size Receptacle, 6 Poles, 1/2" - 14 NPT Threads, Female (90°) to 16 AWG Leads, 0.305m (1.0') Length

**Agency Certification**

CSA	LR6837
UL	E152210

**General**

Product Family	Industrial Receptacles
Series	<a href="#">130013</a>
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	minichange_products
Product Name	Mini-Change
Taxonomy	Circular Industrial Connectors
Type	Single Ended (pigtail)
UPC	78678843963

**Physical**

Coupling Type	External Thread
Gender	Female
Keyway	Single
Length	0.305m
Material - Component	Zinc Die-Cast with Black Epoxy
Mounting Thread Size	1/2" - 14 NPT
Orientation	90° Angle
Panel Mount	N/A
Poles	6
Temperature Range - Operating	-20° to +105°C
Wire Size AWG	16
Wire/Cable Type	UL 1015

**Electrical**

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC/DC

**Material Info**

Engineering Number	1R6005A20A120
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-130013-074-001
---------------	-------------------

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130013](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**