

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300150112](#)  
**Status:** **Active**  
**Overview:** Brad Mini-Change Connectors  
**Description:** Mini-Change C-Size Receptacle with Leads 1/2" - 14 NPT Threads, Male (Straight) 19 Poles, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Receptacles
Series	<a href="#">130015</a>
Comments	C-Size (1-1/8" - 16 UN-2A)
IP Rating	IP67
Overview	<a href="#">Brad Mini-Change Connectors</a>
Product Name	Mini-Change
Taxonomy	Circular Industrial Connectors
Type	Single Ended (pigtail)
UPC	78678846667

**Physical**

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	2.0m
Material - Component	Gray Anodized Aluminum
Mounting Thread Size	PG16
Net Weight	272.155/g
Orientation	Straight
Panel Mount	Front
Poles	19
Temperature Range - Operating	-20° to +80°C
Wire Size AWG	18, 22
Wire/Cable Type	UL 1569

**Electrical**

Current - Maximum per Contact	2.0A
Voltage - Maximum	300V AC/DC

**Material Info**

Engineering Number	3R3N36E80M020
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-130015-009-001
---------------	-------------------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130015 Series](#)