

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300270015](#)
Status: **Active**
Overview: DeviceNet Solutions
Description: Micro-Change (M12) Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, Gray DeviceNet Thin (Drop) Cable, 3.0m (9.84') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Cordsets
 Series [130027](#)
 Connector End A Micro-Change (M12)
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Brass
 Overview [DeviceNet Solutions](#)
 Product Name DeviceNet, Micro-Change (M12)
 Protocol N/A
 Region Europe
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 78678830023

Physical

Cable Diameter 7.24mm (.285")
 Cable Length 3.0m (9.84')
 Color - Cable Jacket Gray
 Coupling Style Threaded
 Gender Male-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPE
 Material - Coupling Nut Die-Cast Zinc
 Material - Plating Mating Gold
 Net Weight 81.410/g
 Orientation Straight to Pigtail
 Poles 5
 Temperature Range - Operating -20° to +80°C
 Wire Size AWG 22
 Wire/Cable Type Thin (Drop)

Electrical


Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number DND02A-M030

Reference - Drawing Numbers

Sales Drawing SD-130027-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000380977_00_000.pdf

CER_4000410292_00_000.pdf

Search Parts in this Series

[130027 Series](#)

This document was generated on 10/20/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION