

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300340006](#)  
**Status:** **Active**  
**Overview:** [Brad Mini-Change Connectors](#)  
**Description:** Mini-Change Trunk Connector, Threaded, Single Keyway, Straight Male, 5 Poles

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

Product Family Field Attachable / Accessories  
 Series [130034](#)  
 Approvals cCSAus certified  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Mini-Change Connectors](#)  
 Product Name Mini-Change  
 Taxonomy Circular Industrial Connectors  
 Type Field Attachable Connector  
 UPC 78172553490

**Physical**

Cable Diameter 5.00-12.00mm (.20-.48")  
 Coupling Type External Thread  
 Diagnostics / LEDs No  
 Diagnostics Port No  
 Gender Male  
 Keyway Single  
 Material - Connector Body Polyamide  
 Material - Coupling Nut Nickel-plated Brass  
 Material - Plating Mating n/a  
 Net Weight 159.000/g  
 Orientation Straight  
 Poles 5  
 Temperature Range - Operating -25°C to +90°C  
 Wire Size AWG N/A

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 36V

**Material Info**

Engineering Number 1A5006-34DN

**Reference - Drawing Numbers**

Sales Drawing SD-130034-002-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2021)10043-DC (17 Jan 2022)

Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

50 Image

Not Relevant

Not Contained

CER\_4000408918\_00\_000.pdf

CER\_4000410292\_00\_000.pdf

**Search Parts in this Series**

[130034 Series](#)