

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300390302](#)
Status: **Active**
Overview: Brad Mini-Change Connectors
Description: DeviceNet Mini-Change Receptacle, 5 Poles, Male (Straight) with DeviceNet Thick Trunk Cable, 1/2" - 14 NPT, 4.0m (13.12') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Receptacles
 Series [130039](#)
 IP Rating IP67
 NEMA Rating NEMA 6
 Overview [Brad Mini-Change Connectors](#)
 Product Name DeviceNet Trunk, Mini-Change
 Taxonomy Circular Industrial Connectors
 Type Single Ended (pigtail)
 UPC 78678847623

Physical

Coupling Type External Thread
 Gender Male
 Keyway Single
 Length 4.0m
 Material - Component Gray Anodized Aluminum
 Mounting Thread Size 1/2" - 14 NPT
 Net Weight 850.800/g
 Orientation Straight
 Panel Mount Front
 Poles 5
 Temperature Range - Operating -20° to +80°C
 Wire Size AWG 15, 18
 Wire/Cable Type Thick Standard Cable

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 300V AC/DC

Material Info

Engineering Number DN5100-M040

Reference - Drawing Numbers

Sales Drawing SD-130039-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c),6(b)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE -

CER_4000410036_00_000.pdf

Declaration of Conformity

ZZCERT_UKCA

CER_4000410293_00_000.pdf

- Declaration of Conformity

Search Parts in this Series

[130039 Series](#)