

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300570003](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Brad RJ-Lnxx, Threaded, RJ-45 Ethernet Field-Attachable Connector for Solid Core Cable

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	130057
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Industrial Ethernet Solutions
Product Name	Brad, RJ-Lnxx
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	78678842476

Physical

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Polycarbonate
Material - Coupling Nut	ABS
Material - Plating Mating	n/a
Net Weight	21.290/g
Orientation	Straight
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	125V DC

Material Info

Engineering Number	ENSAM315
--------------------	----------

Reference - Drawing Numbers

Sales Drawing	SD-130057-002-001
---------------	-------------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000408918_00_000.pdf

CER_4000410285_00_000.pdf

Search Parts in this Series

[130057 Series](#)