

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130060022](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Mini-Change MPIS, 3 Pole Female, 6 Ports with Molded Cable 0.92m Length

**Agency Certification**

CSA LR6837

**General**

Product Family Passive Distribution Boxes  
 Series [130060](#)  
 IP Rating IP67  
 NEMA Rating NEMA 6  
 Overview minichange\_products  
 Product Name Mini-Change  
 Taxonomy Passive Distribution Boxes  
 UPC 78678861898

**Physical**

Bus I/O Mini-Change  
 Cable Connector Orientation Straight  
 Cable Length 0.91m  
 Home Run Cable Length 0.92m  
 Home Run Connector N/A  
 Home Run Interface N/A  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Housing PBT  
 Material - Metal Copper Alloy  
 Material - Plating Mating Gold  
 Orientation Side Mount  
 Poles 3  
 Poles (wired) 3  
 Ports 8  
 Temperature Range - Operating -25°C to +90°C  
 Wiring Configuration Single I/O per Port

**Electrical**

Current - Maximum per Contact 7.0A  
 Functional Wiring Parallel  
 Voltage - Maximum 600V AC/DC

**Material Info**

Engineering Number 409P893-03

**Reference - Drawing Numbers**

Sales Drawing SD-130060-008-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130060](#) Series