

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300640221](#)  
**Status:** **Active**  
**Overview:** BradPower Cordsets and Receptacles  
**Description:** BradPower D-Size (1 3/8"-M35) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 10 AWG, PVC Cable, 6.0m (19.68') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E258922

**General**

Product Family Industrial Cordsets  
 Series [130064](#)  
 Connector End A BradPower D-Size (1 3/8"-M35)  
 Connector End B BradPower D-Size (1 3/8"-M35)  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [BradPower Cordsets and Receptacles](#)  
 Product Name BradPower D-Size  
 Protocol EtherNet  
 Region Europe  
 Type Double Ended  
 UPC 78678862185

**Physical**

Cable Diameter 5.08mm (.200")  
 Cable Length 6.0m (19.68')  
 Color - Cable Jacket Gray  
 Coupling Style Threaded  
 Gender Female-Male  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body PVC  
 Material - Coupling Nut Anodized Aluminum  
 Material - Plating Mating Gold over Nickel  
 Net Weight 65.540/g  
 Orientation Straight to Straight  
 Poles 4  
 Temperature Range - Operating -20°C to +105°C  
 Wire Size AWG 10  
 Wire/Cable Type ST00W, TC-ER Direct Burial

**Electrical**


Current - Maximum per Contact 25.0A  
 Voltage - Maximum 600V

**Material Info**

Engineering Number CC4030A48M060

**Reference - Drawing Numbers**

Sales Drawing SD-130064-065



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[130064 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**