

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300660325](#)
Status: **Active**
Overview: BradPower Cordsets and Receptacles
Description: BradPower C-Size (1 1/8"-M29) Receptacle, 4 Poles, 1/2" - 14 NPT, Male (Straight) to 12/1 AWG Leads, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Industrial Receptacles
 Series [130066](#)
 IP Rating IP67
 Overview [BradPower Cordsets and Receptacles](#)
 Product Name BradPower C-Size
 Taxonomy Circular Industrial Connectors
 Type Single Ended (pigtail)
 UPC 78172500206

Physical

Coupling Type External Thread
 Gender Male
 Keyway Tri-Key
 Length 1.0m
 Material - Component Nickel-plated Brass
 Mounting Thread Size 1/2" - 14 NPT
 Net Weight 77.000/g
 Orientation Straight
 Panel Mount Front
 Poles 4
 Temperature Range - Operating -20° to +90°C
 Wire Size AWG 12
 Wire/Cable Type UL 1015

Electrical

Current - Maximum per Contact 25.0A
 Voltage - Maximum 600V

Material Info

Engineering Number 3R4106A84M0103

Reference - Drawing Numbers

Sales Drawing 1300660319-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)10043-DC (17 Jan 2022)

Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

Not Relevant

Not Reviewed

Not Contained

CER_4000410542_00_000.pdf

Search Parts in this Series

[130066 Series](#)