

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300700019](#)  
**Status:** **Active**  
**Overview:** [BradPower Cordsets and Receptacles](#)  
**Description:** BradPower D-Size (1 3/8"-M35) Female Closure Cap, Internal Threads, 38.35mm Diameter

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">130070</a>
IP Rating	N/A
Material - Contact	N/A
Overview	<a href="#">BradPower Cordsets and Receptacles</a>
Product Name	BradPower D-Size
Taxonomy	Industrial Accessories
Type	Accessory - Closure Cap
UPC	78678855155

**Physical**

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	N/A
Material - Connector Body	Anodized Aluminum
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	98.110/g
Orientation	N/A
Poles	N/A
Temperature Range - Operating	-20°C to +90°C
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

**Material Info**

Engineering Number	55-0298
--------------------	---------

**Reference - Drawing Numbers**

Sales Drawing	SD-130070-005-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[130070 Series](#)