

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300830224](#)  
**Status:** **Active**  
**Overview:** [Reels - Woodhead](#)  
**Description:** Woodhead POW-R-MITE Industrial Duty Cable Reel, 16/3 SOW, 9.14m (30.0') Cord Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**Agency Certification**

CSA LR29921  
 UL E22769

**General**

Product Family Electric Reels  
 Series [130083](#)  
 Cable Length N/A  
 Comments Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.  
 Depth 0.34m (13.50")  
 Duty Industrial  
 Enclosure Rating NEMA 4  
 Height 0.37m (14.50")  
 NEMA Configuration N/A  
 Overview [Reels - Woodhead](#)  
 Product Name POW-R-MITE  
 Taxonomy Electric Reels  
 Type Cable Reel  
 UPC 78678879224  
 Width 244.35mm (9.620")

**Physical**

Cable Movement Ratchet Lock  
 Cord Length 9.14m (30.0')  
 Drum Lock Ratchet  
 Guide Arm 5° increments over 270° Arc  
 Material - Coating Powder Coating  
 Material - Housing Cast Aluminum  
 Mounting Style Rigid  
 Net Weight 16329.312/g  
 Number of Conductors 3  
 Packaging Type Carton  
 Primary Cord/Cable Entry 1" NPT  
 Retraction Weight 1.8kg (4.0 lb)  
 Wire Size AWG 16

**Electrical**

Bulb Included N/A  
 Cord Type 16/3 SOW  
 Current - Maximum per Contact 9.0A  
 GFCI No  
 Lamp Type N/A  
 Lamp Wattage - Maximum N/A  
 On/Off Switch N/A  
 Voltage - Maximum 600V

**Material Info**



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130083 Series](#)

Engineering Number

9224

**Reference - Drawing Numbers**

Sales Drawing

1300830224-000

This document was generated on 08/27/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**