

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300830270](#)
Status: **Active**
Overview: Reels - Woodhead
Description: Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 7.62m (25.0') Cord Length with 15A GFCI Pendant Outlet Box and Ball Stop

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Electric Reels
Series	130083
Cable Length	N/A
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Depth	0.34m (13.50")
Duty	Industrial
Enclosure Rating	NEMA 4
Height	0.37m (14.50")
NEMA Configuration	NEMA 5-15
Overview	Reels - Woodhead
Product Name	POW-R-MITE
Taxonomy	Electric Reels
Type	Cable Reel
UPC	78678834116
Width	244.35mm (9.620")

Physical

Cable Movement	Ratchet Lock
Cord Length	7.62m (25.0')
Drum Lock	Ratchet
Guide Arm	5° increments over 270° Arc
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Number of Conductors	3
Number of Receptacles	2
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Wire Size AWG	12

Electrical


Bulb Included	N/A
Cord Type	12/3 SOW
Current - Maximum per Contact	18.0A
GFCI	Yes
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	120V

Material Info

Engineering Number	9383-3070G
--------------------	------------

Reference - Drawing Numbers

Sales Drawing	1300830270-000
---------------	----------------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130083 Series](#)

This document was generated on 10/10/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION