

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300830775](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead POW-R-MITE Industrial Duty Cable Reel, 16/3 SOW, 15.24m (50.0') Cord Length with 13W Fluorescent Hand Lamp and Ball Stop

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E22769

General

Product Family	Electric Reels
Series	130083
Cable Length	N/A
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag., Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Depth	0.34m (13.50")
Duty	Industrial
Enclosure Rating	NEMA 4
Exclude SD Check	Yes
Height	0.37m (14.50")
NEMA Configuration	N/A
Overview	Reels - Woodhead
Product Literature Order No	987650-8062
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678834642
Width	244.35mm (9.620")


Physical

Cable Movement	Ratchet Lock
Cord Length	15.24m (50.0')
Drum Lock	Ratchet
Guide Arm	5° increments over 270° Arc
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Wire Size AWG	16

Electrical

Bulb Included	Yes
Cord Type	16/3 SOW
Current - Maximum per Contact	9.0A
GFCI	No
Lamp Type	Fluorescent
Lamp Wattage - Maximum	13W
On/Off Switch	Yes
Voltage - Maximum	120V

Material Info



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130083 Series](#)

This document was generated on 09/11/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION