

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300830784](#)
Status: **Active**
Overview: Reels - Woodhead
Description: Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 15.24m (50.0') Cord Length with 15A Pendant Outlet Box and Ball Stop

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR29921

General

Product Family Electric Reels
 Series [130083](#)
 Cable Length N/A
 Comments Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
 Depth 0.34m (13.50")
 Duty Industrial
 Enclosure Rating NEMA 4
 Height 0.37m (14.50")
 NEMA Configuration NEMA 5-15
 Overview [Reels - Woodhead](#)
 Product Name POW-R-MITE
 Taxonomy Electric Reels
 Type Cable Reel
 UPC 78678833818
 Width 244.35mm (9.620")

Physical

Cable Movement Ratchet Lock
 Cord Length 15.24m (50.0')
 Drum Lock Ratchet
 Guide Arm 5° increments over 270° Arc
 Material - Coating Powder Coating
 Material - Housing Cast Aluminum
 Mounting Style Rigid
 Number of Conductors 3
 Number of Receptacles 4
 Packaging Type Carton
 Primary Cord/Cable Entry 1" NPT
 Retraction Weight 1.8kg (4.0 lb)
 Wire Size AWG 12

Electrical

Bulb Included N/A
 Cord Type 12/3 SOW
 Current - Maximum per Contact 18.0A
 GFCI No
 Lamp Type N/A
 Lamp Wattage - Maximum N/A
 On/Off Switch N/A
 Voltage - Maximum 120V

Material Info

Engineering Number 92433-3000



EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130083 Series](#)

Reference - Drawing Numbers
Sales Drawing

1300830784-000

This document was generated on 10/10/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION