

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300870058](#)  
**Status:** **Active**  
**Overview:** [Reels - Woodhead](#)  
**Description:** Woodhead Super-Safeway Heavy Duty Hand Wind Reel, 12/3 SOW, 15.24m (50.0') Cord Length

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR29921  
 UL E19795

**General**

Product Family Electric Reels  
 Series [130087](#)  
 Cable Length N/A  
 Comments Hand Wind Reels are design for heavy duty industrial storage applications  
 Depth 0.34m (13.25")  
 Duty Industrial  
 Enclosure Rating NEMA 1  
 Height 0.45m (17.6")  
 NEMA Configuration NEMA 5-15  
 Overview [Reels - Woodhead](#)  
 Product Name Super-Safeway  
 Taxonomy Electric Reels  
 Type Hand Wind Reel  
 UPC 78678800870  
 Width 241.30mm (9.500")

**Physical**

Cable Movement Manual  
 Cord Length 15.24m (50.0')  
 Drum Lock None  
 Material - Coating Powder Coating  
 Material - Housing Steel  
 Mounting Style N/A  
 Number of Conductors 3  
 Number of Receptacles 1  
 Packaging Type Carton  
 Primary Cord/Cable Entry N/A  
 Retraction Weight N/A  
 Wire Size AWG 12

**Electrical**

Bulb Included N/A  
 Cord Type 12/3 SOW  
 Current - Maximum per Contact 15.0A  
 GFCI No  
 Lamp Type N/A  
 Lamp Wattage - Maximum N/A  
 On/Off Switch N/A  
 Voltage - Maximum 120V

**Material Info**

Engineering Number 930B123



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130087 Series](#)

This document was generated on 10/11/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**