

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300910053](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead Standard Cord Reel, 14/3 SJTOW Cord, 13.72m (45.0') Cord Length with 15A Connector, NEMA 5-15

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E22769

General

Product Family Electric Reels
 Series [130091](#)
 Cable Length 0.457m (1.50')
 Depth 0.30m (11.75")
 Duty Standard
 Enclosure Rating NEMA 1
 Height 0.36m (14.25")
 NEMA Configuration NEMA 5-15
 Overview [Reels - Woodhead](#)
 Product Name Super-Safeway
 Taxonomy Electric Reels
 Type Cord Reel
 UPC 78678833626
 Width 196.85mm (7.750")

Physical

Cable Movement Ratchet Lock
 Cord Length 13.72m (45.0')
 Drum Lock Ratchet
 Guide Arm 2 - Position
 Material - Coating Powder Coating
 Material - Housing Steel/Polycarbonate
 Mounting Style Rigid
 Number of Conductors 3
 Number of Receptacles 1
 Packaging Type Carton
 Primary Cord/Cable Entry N/A
 Retraction Weight 1.4kg (3.0 lb)
 Wire Size AWG 14

Electrical

Bulb Included N/A
 Cord Type 14/3 SJTOW
 Current - Maximum per Contact 11.0A
 GFCI No
 Lamp Type N/A
 Lamp Wattage - Maximum N/A
 On/Off Switch No
 Voltage - Maximum 120V

Material Info

Engineering Number 990-1547

Reference - Drawing Numbers



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130091 Series](#)

This document was generated on 08/27/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION