

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300910064](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead Standard Duty Reel, 14/3 SJTOW Cord, 13.72m (45.0') Cord Length with 13W Fluorescent Hand Lamp and Reel-mounted Switch

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Electric Reels
Series	130091
Cable Length	0.457m (1.50')
Depth	0.30m (11.75")
Duty	Standard
Enclosure Rating	NEMA 1
Height	0.36m (14.25")
NEMA Configuration	NEMA 5-15
Overview	Reels - Woodhead
Product Name	Super-Safeway
Taxonomy	Electric Reels
Type	Cord Reel
UPC	78678833620
Width	196.85mm (7.750")

Physical

Cable Movement	Ratchet Lock
Cord Length	13.72m (45.0')
Drum Lock	Ratchet
Guide Arm	2 - Position
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Wire Size AWG	14

Electrical

Bulb Included	Yes
Cord Type	14/3 SJTOW
Current - Maximum per Contact	11.0A
GFCI	No
Lamp Type	Fluorescent
Lamp Wattage - Maximum	13W
On/Off Switch	Yes
Voltage - Maximum	120V

Material Info

Engineering Number	990A-83
--------------------	---------

Reference - Drawing Numbers

Sales Drawing	1300910064-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130091](#) Series

This document was generated on 08/27/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION