

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300910094](#)
Status: **Active**
Overview: [Reels - Woodhead](#)
Description: Woodhead Standard Cord Reel, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length with 15A GFCI Pendant Outlet Box, One Duplex, NEMA 5-15 Outlet

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR29921

General

Product Family Electric Reels
 Series [130091](#)
 Cable Length 0.457m (1.50')
 Depth 0.30m (11.75")
 Duty Standard
 Enclosure Rating NEMA 1
 Height 0.36m (14.25")
 NEMA Configuration NEMA 5-15
 Overview [Reels - Woodhead](#)
 Product Name Super-Safeway
 Taxonomy Electric Reels
 Type Cord Reel
 UPC 78678833628
 Width 196.85mm (7.750")

Physical

Cable Movement Ratchet Lock
 Cord Length 10.67m (35.0')
 Drum Lock Ratchet
 Guide Arm 2 - Position
 Material - Coating Powder Coating
 Material - Housing Steel/Polycarbonate
 Mounting Style Rigid
 Net Weight 11793.392/g
 Number of Conductors 3
 Number of Receptacles 2
 Packaging Type Carton
 Primary Cord/Cable Entry N/A
 Retraction Weight 1.4kg (3.0 lb)
 Wire Size AWG 12

Electrical

Bulb Included N/A
 Cord Type 12/3 SJTOW
 Current - Maximum per Contact 15.0A
 GFCI Yes
 Lamp Type N/A
 Lamp Wattage - Maximum N/A
 On/Off Switch No
 Voltage - Maximum 120V

Material Info

Engineering Number 997-3070G



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130091](#) Series

Reference - Drawing Numbers
Sales Drawing

SD-130091-025-001

This document was generated on 08/27/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION