

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300940232](#)

Status: **Active**

Overview: [Support Grips](#)

Description: Standard Duty Support Grip, Single Eye, Closed Mesh, Single Weave, Cable Diameter 15.88-19.05mm (.625-.750"), Approximate Break Strength 435.45kg (960 lbs)

Documents:

[Packaging Specification PK-130227-004-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159

General


Product Family	Cable Grips
Series	130094
Eye Type	Single
O-Ring	N/A
Overview	Support Grips
Product Name	Standard Duty
Taxonomy	Cable Grips
Type	Support Grip
UPC	78678835031
Physical	
Approximate Break Strength	435.45kg (960 lbs)
Bale Length	0.203m (8.00")
Body Style	Straight
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.279m (11.00")
Net Weight	587.000/g
Number of Holes	N/A
Thread Size	N/A

Material Info

Engineering Number 35031

Reference - Drawing Numbers

Packaging Specification PK-130227-004-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[130094](#) Series