

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **[1300940279](#)**

Status: **Active**

Overview: [Support Grips](#)

Description: Standard Duty Support Grip, Locking Bale, Closed Mesh, Single Weave, Cable Diameter 38.10-44.20mm (1.500-1.740"), Approximate Break Strength 870.90kg (1920 lbs)

Documents:

[Packaging Specification PK-130227-004-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)



Series image - Reference only

Agency Certification

CSA LR32159

General

Product Family	Cable Grips
Series	130094
Eye Type	Locking Bale
O-Ring	N/A
Overview	Support Grips
Product Name	Standard Duty
Taxonomy	Cable Grips
Type	Support Grip
UPC	78678835095
Physical	
Approximate Break Strength	870.90kg (1920 lbs)
Bale Length	0.457m (18.00")
Body Style	Straight
Cable Diameter	38.10-44.20mm (1.500-1.740")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.432m (17.00")
Number of Holes	N/A
Thread Size	N/A

Material Info

Engineering Number 35095

Reference - Drawing Numbers

Packaging Specification PK-130227-004-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130094](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION