

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300940408](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Standard Duty Support Grip, Offset Eye, Split Rod, Single Weave, Cable Diameter 15.88-19.05mm (.625-.750"), Approximate Break Strength 435.45kg (960 lbs)

**Agency Certification**

CSA LR32159

**General**

Product Family Cable Grips  
 Series [130094](#)  
 Eye Type Offset  
 O-Ring N/A  
 Overview support\_grips  
 Product Name Standard Duty  
 Taxonomy Cable Grips  
 Type Support Grip  
 UPC 78678835301

**Physical**

Approximate Break Strength 435.45kg (960 lbs)  
 Bale Length 0.102m (4.00")  
 Body Style Straight  
 Cable Diameter 15.88-19.05mm (.625-.750")  
 Color - Grommet N/A  
 Gender N/A  
 Material - Body N/A  
 Material - Grip Non-magnetic Tin Bronze Wire  
 Mesh Length 0.279m (11.00")  
 Number of Holes N/A  
 Thread Size N/A

**Material Info**

Engineering Number 35301

**Reference - Drawing Numbers**

Packaging Specification PK-130227-004-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[130094](#) Series