

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300940444](#)

Status: **Active**

Overview:

Description: Heavy Duty Support Grip, Double Eye, Double Weave, Closed Mesh, Cable Diameter 31.75-37.85mm (1.250-1.490"), Approximate Break Strength 2140.96kg (4720 lbs)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
 Series [130094](#)
 Eye Type Double
 O-Ring N/A
 Overview support_grips
 Product Name Heavy Duty
 Taxonomy Cable Grips
 Type Support Grip
 UPC 78678835427

Physical

Approximate Break Strength 2140.96kg (4720 lbs)
 Bale Length 0.254m (10.00")
 Body Style Straight
 Cable Diameter 31.75-37.85mm (1.250-1.490")
 Color - Grommet N/A
 Gender N/A
 Material - Body N/A
 Material - Grip Non-magnetic Tin Bronze Wire
 Mesh Length 0.787m (31.00")
 Number of Holes N/A
 Thread Size N/A

Material Info

Engineering Number 35427

Reference - Drawing Numbers

Packaging Specification PK-130227-004-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130094](#) Series