

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300940531](#)

**Status:** **Active**

**Overview:**

**Description:** Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 4", Cable Diameter 7.62-9.91mm (.300-.390"), Approximate Break Strength 136.08kg (300 lbs)

**Agency Certification**

CSA LR32159

**General**

Product Family	Cable Grips
Series	<a href="#">130094</a>
Eye Type	Single
O-Ring	N/A
Overview	support_grips
Product Name	Fiber Optic
Taxonomy	Cable Grips
Type	Support Grip
UPC	78678836682
<b>Physical</b>	
Approximate Break Strength	136.08kg (300 lbs)
Bale Length	0.229m (9.00")
Body Style	Straight
Cable Diameter	7.62-9.91mm (.300-.390")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.064m (2.50")
Number of Holes	N/A
Thread Size	N/A
<b>Material Info</b>	
Engineering Number	36682
<b>Reference - Drawing Numbers</b>	
Sales Drawing	SD-130094-008-001

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130094](#) Series