

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300940534](#)
Status: **Active**
Overview: [Support Grips](#)
Description: Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 7", Cable Diameter 14.22-18.03mm (.560-.710"), Approximate Break Strength 272.16kg (600 lbs)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family	Cable Grips
Series	130094
Eye Type	Single
O-Ring	N/A
Overview	Support Grips
Product Name	Fiber Optic
Taxonomy	Cable Grips
Type	Support Grip
UPC	78678836685

Physical


Approximate Break Strength	272.16kg (600 lbs)
Bale Length	0.178m (7.00")
Body Style	Straight
Cable Diameter	14.22-18.03mm (.560-.710")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.14m (5.50")
Number of Holes	N/A
Thread Size	N/A

Material Info

Engineering Number 36685

Reference - Drawing Numbers

Sales Drawing SD-130094-008-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130094 Series](#)