

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300950127](#)
Status: **Active**
Overview: [Pulling Grips](#)
Description: Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Short Mesh Length 0.508m (20.00"), Approximate Break Strength 7438.92kg (16400 lbs)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
 Series [130095](#)
 Eye Type Rotating
 O-Ring N/A
 Overview [Pulling Grips](#)
 Product Name Heavy Duty
 Taxonomy Cable Grips
 Type Pulling Grip
 UPC 78678835868

Physical

Approximate Break Strength 7438.92kg (16400 lbs)
 Bale Length N/A
 Body Style Straight
 Cable Diameter 25.40-31.50mm (1.000-1.240")
 Color - Grommet N/A
 Eye Diameter 1 3/8"
 Gender N/A
 Material - Body N/A
 Material - Grip Galvanized Steel
 Mesh Length 0.508m (20.00")
 Number of Holes N/A
 Thread Size N/A

Material Info

Engineering Number 35868

Reference - Drawing Numbers

Sales Drawing SD-130095-106-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130095 Series](#)