

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300950129](#)

Status: **Active**

Overview: [Pulling Grips](#)

Description: Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Short Mesh Length 0.635m (25.00"), Approximate Break Strength 12337.71kg (27200 lbs)

Documents:

[Drawing \(PDF\)](#)

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family	Cable Grips
Series	130095
Eye Type	Rotating
O-Ring	N/A
Overview	Pulling Grips
Product Name	Heavy Duty
Taxonomy	Cable Grips
Type	Pulling Grip
UPC	78678835870

Physical

Approximate Break Strength	12337.71kg (27200 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	38.10-50.55mm (1.500-1.990")
Color - Grommet	N/A
Eye Diameter	1 5/8"
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.635m (25.00")
Number of Holes	N/A
Thread Size	N/A

Material Info

Engineering Number 35870

Reference - Drawing Numbers

Sales Drawing SD-130095-106-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130095 Series](#)