

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300950149](#)
Status: **Active**
Overview: [Pulling Grips](#)
Description: Light Duty Wire Mesh Pulling Grip, Single Weave, Flexible Rope Eye, Short Mesh Length 0.419m (16.50"), Approximate Break Strength 2630.84kg (5800 lbs)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
 Series [130095](#)
 Eye Type Flexible
 O-Ring N/A
 Overview [Pulling Grips](#)
 Product Name Light Duty
 Taxonomy Cable Grips
 Type Pulling Grip
 UPC 78678835904

Physical

Approximate Break Strength 2630.84kg (5800 lbs)
 Bale Length N/A
 Body Style Straight
 Cable Diameter 25.40-31.50mm (1.000-1.240")
 Color - Grommet N/A
 Gender N/A
 Material - Body N/A
 Material - Grip Galvanized Steel
 Mesh Length 0.419m (16.50")
 Number of Holes N/A
 Thread Size N/A

Material Info

Engineering Number 35904

Reference - Drawing Numbers

Sales Drawing SD-130095-101-001



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130095](#) Series