

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300950154](#)  
**Status:** **Active**  
**Overview:** [Pulling Grips](#)  
**Description:** Light Duty Wire Mesh Pulling Grip, Single Weave, Flexible Rope Eye, Short Mesh Length 0.603m (23.75"), Approximate Break Strength 5896.70kg (13000 lbs)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**Agency Certification**

CSA LR32159

**General**

Product Family Cable Grips  
 Series [130095](#)  
 Eye Type Flexible  
 O-Ring N/A  
 Overview [Pulling Grips](#)  
 Product Name Light Duty  
 Taxonomy Cable Grips  
 Type Pulling Grip  
 UPC 78678835909

**Physical**

Approximate Break Strength 5896.70kg (13000 lbs)  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 63.50-75.95mm (2.500-2.990")  
 Color - Grommet N/A  
 Gender N/A  
 Material - Body N/A  
 Material - Grip Galvanized Steel  
 Mesh Length 0.603m (23.75")  
 Number of Holes N/A  
 Thread Size N/A

**Material Info**

Engineering Number 35909

**Reference - Drawing Numbers**

Sales Drawing SD-130095-101-001



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130095](#) Series