

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300950175](#)

**Status:** **Active**

**Overview:** [Pulling Grips](#)

**Description:** Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Short Mesh Length 0.61m (24.00"), Approximate Break Strength 4354.49kg (9600 lbs)

**Documents:**

[Drawing \(PDF\)](#)

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159

**General**

Product Family Cable Grips  
 Series [130095](#)  
 Comments Cable Eye Thickness 5/16"  
 Eye Type Flexible  
 O-Ring N/A  
 Overview [Pulling Grips](#)  
 Product Name Medium Duty  
 Taxonomy Cable Grips  
 Type Pulling Grip  
 UPC 78678835943

**Physical**

Approximate Break Strength 4354.49kg (9600 lbs)  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 25.40-37.85mm (1.000-1.490")  
 Color - Grommet N/A  
 Gender N/A  
 Material - Body N/A  
 Material - Grip Galvanized Steel  
 Mesh Length 0.61m (24.00")  
 Number of Holes N/A  
 Thread Size N/A

**Material Info**

Engineering Number 35943

**Reference - Drawing Numbers**

Sales Drawing SD-130095-103-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**Search Parts in this Series**

[130095 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**