

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300950178](#)  
**Status:** **Active**  
**Overview:** [Pulling Grips](#)  
**Description:** Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Short Mesh Length 0.61m (24.00"), Cable Range 63.50-75.90mm (2.500-2.990"), Approximate Break Strength 11113.01kg (24500 lbs)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)



**Agency Certification**

CSA LR32159

**General**

Product Family	Cable Grips
Series	<a href="#">130095</a>
Comments	Cable Eye Thickness 1/2"
Eye Type	Flexible
O-Ring	N/A
Overview	<a href="#">Pulling Grips</a>
Product Name	Medium Duty
Taxonomy	Cable Grips
Type	Pulling Grip
UPC	78678835946

**Physical**

Approximate Break Strength	11113.01kg (24500 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	63.50-75.95mm (2.500-2.990")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.61m (24.00")
Number of Holes	N/A
Thread Size	N/A

**Material Info**

Engineering Number 35946

**Reference - Drawing Numbers**

Sales Drawing SD-130095-103-001

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130095 Series](#)