

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300960058](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: Liquid-Tight Grip Strain Relief, 3/8" NPT, 90° Angle Male, Mesh Length 0.067m (2.625")

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
 UL E61303

General

Product Family Cable Grips
 Series [130096](#)
 Eye Type N/A
 NEMA Rating NEMA 4
 O-Ring N/A
 Overview [Strain-Relief Cord Grips](#)
 Product Name Liquid-Tight
 Taxonomy Cable Grips
 Type Strain Relief Grip
 UPC 78678836443
 Use With 3/8" NPT MAX-LOC Lock Nut [1300990142](#) , 3/8" NPT MAX-LOC Gasket [1300990148](#)

Physical

Approximate Break Strength N/A
 Bale Length N/A
 Body Style 90° Angle
 Cable Diameter N/A
 Color - Grommet N/A
 Gender Male
 Material - Body Malleable Iron, Zinc Plated Steel
 Material - Grip Stainless Steel
 Mesh Length 0.067m (2.625")
 Number of Holes N/A
 Thread Size 3/8" NPT

Material Info

Engineering Number 36443

Reference - Drawing Numbers

Sales Drawing SD-130096-101-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130096 Series](#)