

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300970160](#)  
**Status:** **Active**  
**Overview:** Strain-Relief Cord Grips  
**Description:** Deluxe Cord Grips Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 4.75-6.35mm (.187-.250")

**Documents:**

[Drawing \(PDF\)](#)  
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159  
 UL E76954

**General**

Product Family Cable Grips  
 Series [130097](#)  
 Eye Type N/A  
 Hazardous Locations Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2  
 NEMA Rating NEMA 4  
 O-Ring N/A  
 Overview [Strain-Relief Cord Grips](#)  
 Product Name Deluxe Cord  
 Taxonomy Cable Grips  
 Type Strain Relief Grip  
 UPC 78678836250  
 Use With 1/2" NPT MAX-LOC Lock Nut [1300990143](#) , MAX-LOC O-Ring, 1/2" NPT [1301800314](#) , 1/2" NPT MAX-LOC Gasket [1300990149](#)

**Physical**

Approximate Break Strength N/A  
 Bale Length 0.051m (2.00")  
 Body Style Straight  
 Cable Diameter 4.75-6.35mm (.187-.250")  
 Color - Grommet Orange  
 Gender Male  
 Material - Body Aluminum  
 Material - Grip Stainless Steel  
 Mesh Length 0.102m (4.00")  
 Net Weight 42.184/g  
 Number of Holes N/A  
 Thread Size 1/2" NPT

**Material Info**

Engineering Number 36250

**Reference - Drawing Numbers**

Sales Drawing SD-130097-103-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[130097 Series](#)