

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300970191](#)  
**Status:** **Active**  
**Overview:** Strain-Relief Cord Grips  
**Description:** Deluxe Cord Grips Strain Relief, 3/4" NPT, Straight Female, Cable Diameter 6.35-9.53mm (.250-.375")

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**Agency Certification**

CSA LR32159

**General**

Product Family Cable Grips  
 Series [130097](#)  
 Eye Type N/A  
 Hazardous Locations Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2  
 NEMA Rating NEMA 4  
 O-Ring N/A  
 Overview Strain-Relief Cord Grips  
 Product Name Deluxe Cord  
 Taxonomy Cable Grips  
 Type Strain Relief Grip  
 UPC 78678836290  
 Use With 3/4" NPT MAX-LOC Lock Nut [1300990144](#) , 3/4" NPT MAX-LOC Gasket Sealing Ring [1300990150](#) , 3/4" NPT MAX-LOC O-Ring [1301800333](#)

**Physical**

Approximate Break Strength N/A  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 6.35-9.53mm (.250-.375")  
 Color - Grommet N/A  
 Gender Female  
 Material - Body Aluminum  
 Material - Grip Stainless Steel  
 Mesh Length N/A  
 Number of Holes N/A  
 Thread Size 3/4" NPT

**Material Info**

Engineering Number 36290

**Reference - Drawing Numbers**

Sales Drawing SD-130097-106-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130097 Series](#)