

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300970295](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: Deluxe Cord Grips Strain Relief, 1" NPT, 90° Angle Male, Cable Diameter 11.10-14.27mm (.437-.562")

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
 UL E76954

General

Product Family Cable Grips
 Series [130097](#)
 Eye Type N/A
 Hazardous Locations Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2
 NEMA Rating NEMA 4
 O-Ring N/A
 Overview [Strain-Relief Cord Grips](#)
 Product Name Deluxe Cord
 Taxonomy Cable Grips
 Type Strain Relief Grip
 UPC 78678836829
 Use With MAX-LOC Lock Nut 1" NPT [1300990145](#) , MAX-LOC Gasket Sealing Ring 1" NPT [1300990151](#) , MAX-LOC O-Ring, 1" NPT [1301800334](#)

Physical

Approximate Break Strength N/A
 Bale Length N/A
 Body Style 90° Angle
 Cable Diameter 11.10-14.27mm (.437-.562")
 Color - Grommet N/A
 Gender Male
 Material - Body Aluminum
 Material - Grip Stainless Steel
 Mesh Length N/A
 Number of Holes N/A
 Thread Size 1" NPT

Material Info

Engineering Number 36829

Reference - Drawing Numbers

Sales Drawing SD-130097-108-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[130097 Series](#)