

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980092](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 14.27-15.88mm (.562-.625")

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
 UL E76954

General

Product Family Cable Grips
 Series [130098](#)
 Eye Type N/A
 NEMA Rating NEMA 6P
 O-Ring Yes
 Overview [Strain-Relief Cord Grips](#)
 Product Name MAX-LOC
 Taxonomy Cable Grips
 Type Strain Relief Grip
 UPC 78678855342
 Use With 1/2" NPT MAX-LOC Lock Nut [1300990143](#)

Physical

Approximate Break Strength N/A
 Bale Length N/A
 Body Style Straight
 Cable Diameter 14.27-15.88mm (.562-.625")
 Color - Grommet N/A
 Gender Male
 Material - Body Nylon
 Material - Grip N/A
 Mesh Length N/A
 Net Weight 30.390/g
 Number of Holes 1
 Thread Size 1/2" NPT

Material Info

Engineering Number 5534W



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

China RoHS

Search Parts in this Series

[130098](#) Series