

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980136](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male, Cable Diameter 12.70-15.88mm (.500-.625")

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
 UL E76954

General

Product Family Cable Grips
 Series [130098](#)
 Eye Type N/A
 NEMA Rating NEMA 3R
 O-Ring No
 Overview [Strain-Relief Cord Grips](#)
 Product Name MAX-LOC
 Taxonomy Cable Grips
 Type Strain Relief Grip
 UPC 78678872129
 Use With MAX-LOC Lock Nut 1" NPT [1300990145](#) , MAX-LOC Gasket Sealing Ring 1" NPT [1300990151](#) , MAX-LOC O-Ring, 1" NPT [1301800334](#)

Physical


Approximate Break Strength N/A
 Bale Length N/A
 Body Style Straight
 Cable Diameter 12.70-15.88mm (.500-.625")
 Color - Grommet N/A
 Gender Male
 Material - Body Nylon
 Material - Grip N/A
 Mesh Length N/A
 Number of Holes 1
 Thread Size 1" NPT

Material Info

Engineering Number 5548

Reference - Drawing Numbers

Sales Drawing 1300980132-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130098 Series](#)