

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300980208](#)  
**Status:** **Active**  
**Overview:** Strain-Relief Cord Grips  
**Description:** MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, 90° Angle Male, Cable Diameter 5.72mm (.225"), with O-Ring

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159  
 UL E76954

**General**


Product Family Cable Grips  
 Series [130098](#)  
 Eye Type N/A  
 NEMA Rating NEMA 6P  
 O-Ring Yes  
 Overview Strain-Relief Cord Grips  
 Product Name MAX-LOC  
 Taxonomy Cable Grips  
 Type Strain Relief Grip  
 UPC 78678838470  
 Use With 1/2" NPT MAX-LOC Lock Nut [1300990143](#)

**Physical**

Approximate Break Strength N/A  
 Bale Length N/A  
 Body Style 90° Angle  
 Cable Diameter 5.72mm (.225")  
 Color - Grommet N/A  
 Gender Male  
 Material - Body Nylon  
 Material - Grip N/A  
 Mesh Length N/A  
 Number of Holes 2, 3, or 4  
 Thread Size 1/2" NPT

**Material Info**

Engineering Number 5595-004W



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130098 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**