

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300990104](#)  
**Status:** **Active**  
**Overview:** [Strain-Relief Cord Grips](#)  
**Description:** MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 15.88-19.05mm (.625-.750"), Stainless Steel Mesh and Nylon Compression Nut

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159

**General**

Product Family Cable Grips  
 Series [130099](#)  
 Eye Type N/A  
 NEMA Rating NEMA 3R  
 O-Ring No  
 Overview [Strain-Relief Cord Grips](#)  
 Product Name MAX-LOC  
 Taxonomy Cable Grips  
 Type Strain Relief Grip  
 UPC 78678855420  
 Use With 3/4" NPT MAX-LOC Lock Nut [1300990144](#) , 3/4" NPT MAX-LOC Gasket Sealing Ring [1300990150](#) , 3/4" NPT MAX-LOC O-Ring [1301800333](#)

**Physical**

Approximate Break Strength N/A  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 15.88-19.05mm (.625-.750")  
 Color - Grommet Orange  
 Gender Male  
 Material - Body Nylon  
 Material - Grip Stainless Steel  
 Mesh Length N/A  
 Number of Holes 1  
 Thread Size 3/4" NPT

**Material Info**

Engineering Number 5542M

**Reference - Drawing Numbers**

Sales Drawing SD-130099-003-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130099 Series](#)