

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300990177](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC/Watertite Cord Grips, 1" NPT, Straight Male, Body Size F4, Cable Diameter 12.70-15.88mm (.500-.625")

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|----------------|--|
| Product Family | Cable Grips |
| Series | 130099 |
| Eye Type | N/A |
| NEMA Rating | NEMA 3R |
| O-Ring | N/A |
| Overview | Strain-Relief Cord Grips |
| Product Name | MAX-LOC, Watertite |
| Taxonomy | Cable Grips |
| Type | Strain Relief Grip |
| UPC | 78678856364 |
| Use With | MAX-LOC Lock Nut 1" NPT 1300990145 , MAX-LOC Gasket Sealing Ring 1" NPT 1300990151 , MAX-LOC O-Ring, 1" NPT 1301800334 |

Physical

| | |
|----------------------------|----------------------------|
| Approximate Break Strength | N/A |
| Bale Length | N/A |
| Body Style | Straight |
| Cable Diameter | 12.70-15.88mm (.500-.625") |
| Color - Grommet | N/A |
| Gender | Male |
| Material - Body | Nylon |
| Material - Grip | Stainless Steel |
| Mesh Length | N/A |
| Number of Holes | 1 |
| Thread Size | 1" NPT |

Material Info

Engineering Number 5636M

Reference - Drawing Numbers

Sales Drawing SD-130099-007-001



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130099 Series](#)