

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300990180](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC/Watertite Cord Grips, 1" NPT, Straight Male, Body Size F4, Cable Diameter 15.88-19.05mm (.625-.750"), Non-Metallic

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Grips
Series	130099
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	N/A
Overview	Strain-Relief Cord Grips
Product Name	MAX-LOC, Watertite
Taxonomy	Cable Grips
Type	Strain Relief Grip
UPC	78678872107
Use With	MAX-LOC Lock Nut 1" NPT 1300990145 , MAX-LOC Gasket Sealing Ring 1" NPT 1300990151 , MAX-LOC O-Ring, 1" NPT 1301800334

Physical


Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Nylon
Mesh Length	N/A
Number of Holes	1
Thread Size	1" NPT

Material Info

Engineering Number	5637NM
--------------------	--------

Reference - Drawing Numbers

Sales Drawing	SD-130099-008-001
---------------	-------------------



EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130099 Series](#)