

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300990189](#)  
**Status:** **Active**  
**Overview:** Strain-Relief Cord Grips  
**Description:** MAX-LOC/Watertite Cord Grips, 1/2" NPT, Straight Male, Body Size F2 5 7/8", Cable Diameter 12.70-14.27mm (.500-.562")

**Documents:**

[Drawing \(PDF\)](#)  
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Grips
Series	<a href="#">130099</a>
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	N/A
Overview	<a href="#">Strain-Relief Cord Grips</a>
Product Name	MAX-LOC, Watertite
Taxonomy	Cable Grips
Type	Strain Relief Grip
UPC	78678831511
Use With	1/2" NPT MAX-LOC Lock Nut <a href="#">1300990143</a> , MAX-LOC O-Ring, 1/2" NPT <a href="#">1301800314</a> , 1/2" NPT MAX-LOC Gasket <a href="#">1300990149</a>

**Physical**

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	12.70-14.27mm (.500-.562")
Color - Grommet	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Stainless Steel
Mesh Length	N/A
Number of Holes	1
Thread Size	1/2" NPT

**Material Info**

Engineering Number	5647M
--------------------	-------

**Reference - Drawing Numbers**

Sales Drawing	SD-130099-007-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130099 Series](#)