

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020207](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway Rubber Hand Lamp with Switch

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130102](#)
 NEMA Configuration N/A
 Outlet None
 Overview [Hand Lamps](#)
 Product Name Super-Safeway
 Taxonomy Lamps and Lights
 Type Hand Lamps
 UPC 78678860920

Physical

Cord Length - Primary 7.62m (25.0')
 Cord Length - Secondary N/A
 Depth 80.01mm (3.150")
 Duty Industrial
 Guard Included No
 Guard Type N/A
 Height 174.63mm (6.875")
 Length N/A
 Material - Guard N/A
 Mounting Style Hand Held
 Net Weight 400.975/g
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Cord Type - Primary 16/3 SOOW
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 240V

Material Info

Engineering Number 1174



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130102 Series](#)